









ITEM	DESCRIPTION			
1	<b>ISOLATION TRANSFORMER</b>			
	KVA	VOLTAGE		FREQ.
		PRIMARY	SECONDARY	
7.5 10	120 208 277 480	120 208 220	60	
<b>INTERIOR ASSEMBLY</b>				
2	<b>PRIMARY MAIN BREAKER:</b>			
3	<b>BRANCH BREAKERS*</b>	<b>QTY</b>		
		15 A		
		20 A		
	30 A			
4	<b>LINE ISOLATION MONITOR (LIM2010)</b>			
5	<b>CP-LIM2010 CONNECTOR PLATE</b>			
6	<b>GROUND BUS</b>			
7	<b>COMMUNICATION GATEWAY:</b> <input type="checkbox"/> YES <input type="checkbox"/> NO			
8	<b>FAULT LOCATION SYSTEM:</b> <input type="checkbox"/> YES <input type="checkbox"/> NO			
9	<b>CURRENT MONITORING SYSTEM:</b> <input type="checkbox"/> YES <input type="checkbox"/> NO			
10	<b>TRANSFORMER LOAD MONITOR:</b> <input type="checkbox"/> YES <input type="checkbox"/> NO			
11	<b>RECEPTACLE PLATE CONFIGURATION: SEE SHEET 2</b>			
12	<b>FRONT TRIM: T6826R</b>			
13	<b>BACKBOX: B662408F</b>			

\* 16 BREAKERS MAX 2 POLE, 10 kAIC


**GENERAL NOTES:**  
 1. GALVANIZED ROHS COMPLIANT STEEL BOX CONSTRUCTED IN ACCORDANCE WITH UL50.  
 2. FRONT TRIM, TYPE 304 SS WITH #4 POLISH FINISH.  
 3. BOLT-ON CHASSIS FASTENS TO STUDS IN BOX.

PROJECT:		TITLE:	
SALES ORDER		DWG. NO.	
QTY.			
MODEL			
ARTICLE #		REV	
DRAWN BY			
APPROVED BY		SHEET 1 OF 2	
 420 Eagleview Blvd. Exton, PA 19341-1116 1-800-356-4266			
		INT REF. 446 0008 R1	


THE FOLLOWING RECEPTACLES CAN BE USED AT LOCATIONS "A" - "F"			
ABRV.	TYPE OF RECEPTACLES (120V)		
NN	NONE		
SR	NEMA 5-20R SINGLE, RED, HOSPITAL GRADE		
SI	NEMA 5-20R SINGLE, IVORY, HOSPITAL GRADE		
SW	NEMA 5-20R SINGLE, WHITE, HOSPITAL GRADE		
DR	NEMA 5-20R DUPLEX, RED, HOSPITAL GRADE		
DI	NEMA 5-20R DUPLEX, IVORY, HOSPITAL GRADE		
DW	NEMA 5-20R DUPLEX, WHITE, HOSPITAL GRADE		
TB	TWIST-TO-LOCK, BLACK #623000		
BS	BRITISH STANDARD		
THE FOLLOWING RECEPTACLES CAN BE USED AT LOCATIONS "A" - "F"			
ABRV.	TYPE OF RECEPTACLES (208V)		
Y8	NEMA L6-30R 30A/250V TWIST		
THE FOLLOWING GROUND JACKS CAN BE USED AT LOCATIONS "G1" - "G4"			
ABRV.	GROUND JACK		
G	30 A GROUND JACK, HOSPITAL GRADE, TWIST-TO-LOCK		



NOTE: UP TO SIX RECEPTACLES MAY BE USED AT LOCATIONS "A" - "F" AND UP TO FOUR GROUND JACKS MAY BE USED ON THE RECEPTACLE PLATE AT LOCATIONS DESIGNATED "G" PER SYSTEM

PROJECT:			
SALES ORDER		TITLE:	
QTY.			
MODEL			
ARTICLE #		 420 Eagleview Blvd. Exton, PA 19341-1116 1-800-356-4266	DWG. NO.
DRAWN BY			REV
APPROVED BY			
			SHEET 2 OF 2

ITEM	DESCRIPTION
1	ISOLATION TRANSFORMER
2	PRIMARY MAIN BREAKER
3	BRANCH CIRCUIT BREAKERS (16 BREAKERS MAX, 2 POLE, 10 kAIC)
4	LINE ISOLATION MONITOR (LIM2010)
5	CP-LIM2010 CONNECTOR PLATE
6	GROUND BUS
7	DISTRIBUTION BLOCK
8	RECEPTACLES (MAX 6)
9	LOAD MONITOR (STW3)
10	ACCESSORY TERMINAL BLOCK (ATB)
11	SHIELDED TWISTED PAIR CABLE
12	BRANCH LOAD MONITOR (CMS460)
13	FAULT MONITOR (EDS441)
14	COMMUNICATIONS (COM465IP)



- NOTES:**
1. Type XHHW wire with a dielectric constant of less than 3.5 is recommended for all branch circuit field wiring.
  2. Polarity shall be observed in all instances.
  3. Size of all conductors shall be in accordance with all UL, NEC, NFPA and State Fire Marshall requirements.
  4. All remote indication circuitry shall be low voltage and will not contribute leakage to the system.
  5. When other panels/units with RS-485 communication are added onto panel, slide switch "R" on bottom of unit must be positioned in the "off" position. If additional RS-485 related equipment is not connected, slide "R" switch must be in the "on" position.
  6. Quantity of branch breakers (CB1 - CB16), CTs (CT1 - CT12), EDS441 (EDS1 & EDS2), and CMS460 (CMS1 & CMS2) shown for reference only. See elevation drawing for specific values provided.
  7. Quantity of and style of receptacles (R1 - R6) shown for reference only. See elevation drawing for specific values provided.
  8. Customer connections for daisy-chaining RS-485 equipment, if required.

<b>TITLE:</b> MIP WIRING DIAGRAM W/ RECEPTACLES, STW3, CMS460, EDS441, & COM465IP	<b>DRAWN BY:</b> T. COYLE	02/13/20	 420 Eagleview Blvd. Exton, PA 19341-1116 1-800-356-4266	<b>DWG. NO.:</b> 442 0036	<b>REV:</b> 2
	<b>APPROVED BY:</b>				SHEET 1 OF 1